



COLPHENE LIQUID MEMBRANE

LIQUID-APPLIED DETAILING COMPOUND

Order No. *

*Contact Customer Service for Order Number and Availability.

DESCRIPTION

COLPHENE LIQUID MEMBRANE is a two component, elastomeric, solvent free, cold applied material used in conjunction with a variety of Soprema waterproofing membranes.

BASIC USE & APPLICATION

COLPHENE LIQUID MEMBRANE is an accessory product. Please refer to SOPREMA Guide Specifications & approved Details for specific application information.

For use with COLPHENE 60 & COLPHENE 3000:

COLPHENE LIQUID MEMBRANE is designed to be used as a fillet and/or reinforcement under Colphene 60/3000 membranes at inside and outside corners, penetrations/projections and membrane terminations.

For use with COLPHENE BSW (F):

COLPHENE LIQUID MEMBRANE is designed to be used as a membrane adhesive to seal end-laps and/or reinforcement at penetrations/projections and membrane terminations.

All work surfaces should be clean, dry, free of dirt, dust, debris, oils and other contaminants that may result in surfacing that is unsound.

- Keep temperature of cartridges between 65 and 85° F (18 - 29° C) twenty-four hours prior to use. Do not store in direct sunlight or high temperatures exceeding 90° F (32° C).
- Using a utility knife, remove the molded tips at the groove from the mixing head.
- Place the cartridge in to the appropriate applicator (label side up).
- Apply Colphene Liquid Membrane as recommended by Soprema. In order to avoid an initial inconsistent mix, the first small amount (approximately 12") of material from each cartridge should be discarded. NOTE: When sealing endlaps of Colphene BSW (F), apply liquid membrane and spread using approved hand trowel per Soprema recommendations.
- Once the approved sheet membrane is installed, immediately roll to ensure positive contact between Colphene Liquid Membrane and the sheet membrane.
- Partial cartridges can be applied at a later date by simply plugging the cartridges with the provided half moon plugs and using a new mixing tip.

PACKAGING & COVERAGE

- Colphene Liquid Membrane is packaged in four (4) 1.5 L cartridges per case.
- Each cartridge will produce in a range of 50-75 linear feet of 3/4"- 1" wide beads.
- Coverage rates may vary when used over irregular surfaces.
- NOTE: Colphene BSW (F) endlaps are six inches (6") long and thirty-six inches (36") wide. Apply two (2) beads across the width (36") of the roll and spread using an approved hand trowel or putty knife.